



Montageanleitung / Notice de montage / Assembly instruction

Assembly diagram for the base of the cabinet. The diagram shows the base panel being attached to the runners. The required hardware is listed in the top right:


- Ø5mm: 4x
- 16x: 16x
- 3,5x15: 2x
- 4x: 4x
- 6x: 6x
- 2x: 2x

The diagram also shows the attachment of the base panel to the runners using 3,5x15 screws. The required hardware for this step is listed in the bottom right:

- 3,5x15: 12x
- 25mm: 2x
- 3,5x15: 2x








Die Einstellung der Auszug-Blende
bitte durch drehen an den einzelnen
Rehlingstangen vornehmen.
(heranhohlen oder wegdrücken)



SPU 50 Variante Blocktype

Montageanleitung / Notice de montage / Assembly instruction

Flex-Well Vertriebs GmbH
Industriestr. 80
32120 Hiddenhausen
info@flex-well.de



H 80 / H 100 / HG 100 / HGH 100

Varianto

Montageanleitung / Notice de montage / Assembly instruction

Flex-Well Vertriebs GmbH
Industriestr. 80
32120 Hiddenhausen
info@flex-well.de

